


DAIRY PACK RM12C | CUP FILLER



DAIRY PACK RM12C Basics

- Cup FS machine for dairy and food products
- Suitable for paper, plastic, glass and aluminum
- RM12C integrated fillers are designed for fast product change-over and up to 3 different formats
- Volume: 90g to 1000g
- Speed: up to 43,200 cups per hour

DAIRY PACK RM12C Strengths

- High Cup and Product Flexibility
- Ergonomic Operation and Maintenance
- Gentle Product Handling

DAIRY PACK RM12C has been designed for yogurt, deserts, flan, cream, spreadable cheese, butter, dips

DAIRY PACK RM12C | CUP AND PRODUCT HIGH FLEXIBILITY



PLASTIC CUPS

Stackable

Cup Platform 55 to 125mm
Cup Height 40 to 150mm
Product Example: Greek Yogurt



PAPER CUPS

Stackable


Cup Platform 55 to 125mm
Cup Height 40 to 150mm
Product Example: Stirred Yogurt



GLASS CUPS

Non-Stackable

Cup Platform 55 to 95mm
Cup Height up to 120mm
Product Example: Sour Cream



ALUMINUM CUPS

Stackable

Cup Platform 55 to 125mm
Cup Height 40 to 150mm
Product Example: Chocolate Dessert



DESSERTS & CREAM



DAIRY PRODUCTS

High Cup and Product Flexibility


- Up to 3 different formats with possibility of multi-layer products (up to 3 fillers)
- Production speed up to 43,200 cups/hour
- Customizable speed up to 30 cycles per minute
- Footprint (m) : 14L x 5.5W x 3H
- Filling various formats from 90 to 1000g
- Materials: Plastic, Paper, Glass and Aluminum

Ergonomic Operation and Maintenance

- Machine stations can be added to fit your needs (optional cup inserter, decontamination, filling stations, control stations, lid or overcap, topper...)
- Conceived for fast and efficient change-over
- High visibility on stations and tooling
- High accessibility for inspections, maintenance and cleaning operations
- Customizable HMI visualization for optimized production reporting

Gentle Product Handling

- Suitable for most homogeneous and pumpable products with fruit particulates
- Synerlink offer a global commitment for hygienic, integrity and accuracy of the filled products
- Filler device outside the filling area for ultra-clean hygiene and extractable filler heads for optimized safety in CIP
- Available test filler for customer product optimization and faster ramp-up



Synerlink

1 rue de la Boulaye

95650 Puiseux-Pontoise France

t. +33 (0) 1 30 15 29 30

synerlink.com

barrywehmiller

